

COVAL

vacuum managers

just plug it in

pre-set mini-vacuum switch







Strengths

RELIABILITY

- High mechanical resistance thanks to robust aluminum body.
- Compact and ultra light body allows its installation close to the application while improving the reliability of the signal.

PRECISION/SECURITY

- Short response time thanks to the installation close to the suction pads.
- Guarantees precision during the usage thanks to the pre-set vacuum level.
- Available in two pre-set vacuum levels 30 and 50%.
- 4 visual LED indicators with 360° visibility.
- Pre-set vacuum level helps to guarantee the security and avoid unforeseen risks resulting from maintenance operations.


CONNECTIONS

- Two vacuum connection possibilities: push fitting Ø6 mm or threading 1/8" BSPP male.
- M8 connection 3-pin.

SIMPLE AND ECONOMIC

- Ideal for the application which needs a simple "object gripped" signal.
- Efficient and economic solution for all applications with an individual vacuum generator for each suction pad.


General characteristics



- Maximum overpressure: 3 bar.
- Pre-set values for output contact:
- 30 %
- 50 %
- Hysteresis: 10 % of max. vacuum.
- Current supply: 24 V DC (18 V DC mini/ 30 V DC max).
- Current draw: < 30 mA.
- Switching power: 100 mA.
- Response time: 4 ms

- Function according to the output connection: - PNP NO/NC.
 - NPN NO/NC.
- Visual indicator: 4 red LEDS at 360°.
- Electrical connection: M8 male 3-pin.
- Materials: Aluminum/Brass/PU.
- Degree of Protection: IP40.
- Temperature range: -25 to 85°C.
- Weight: 15g.
- Endurance: 1 million cycles minimum.

To order




EXAMPLE OF A STANDARD MODULE:




(mini-vacuum switch PSR with 30% pre-set vacuum range, vacuum connection through push fitting for 6mm OD tube).

M8 ELECTRICAL CONNECTORS

- Screw type female connectors.
- PVC cable with 2m length, pre-assembled 3 wires.
- Degree of protection IP 65.









COVAL VACUUM TECHNOLOGY INC. 212-112 Powell Drive Raleigh, NC 27606 Phone: (919) 233-4855

Fax: (919) 233-4854